


S/N	DESCRIPTION	APPROVED	DATE
1			
2			
3			
4			



BNC video connector cable (RG59), double shielded

Connectors:

2x BNC male

Contacts:

nickel-plated (gold-plated pins)

Conductor area:

0.324 mm²

AWG:

22

Composition of conductor: 1 x 0.643 mm

Conductor material:

CCS

Insulation material:

PE

Jacket material:

PVC

Conductor resistance:

 $300 \pm 10 \Omega/\text{km}$

Shielding:

30 % coverage

Capacitance:


 $58 \pm 5 \text{ pF/m}$

Cable OD:

 $6.0 \pm 0.2 \text{ mm}$

Weight:

41 ± 2 g/m

13				Tolerance (mm)			
12				Wire harness size	Trunk	Protection tube	Positioning space
11				$L \leq 200$	+20 -10		± 5
10				$200 < L \leq 500$	+25 -10		± 5
9				$500 < L \leq 1000$	+40 -20		± 10
8				$1000 < L \leq 2000$	+60 -30		± 20
7				$2000 < L \leq 3000$	+80 -30		± 30
6				$3000 < L \leq 5000$	+80 -30		± 30
5				$L > 5000$	+100 -50		± 40
4							
3							
2							
1							
SYM	Name	Description	Remarks				

APPROVED	Shen Juan		
CHECKED	Li Jie		
DRAWN	Zhang Yining	Customer :	Date : 2023-10-19
UNIT	mm	DRAWING NO.	SIZE:
		BNC-075-3.0	A4
REV	1	CUSTOMER NO.	PAGE:
			1/1