

**NEW**

OTTO SF12

IP68 Elite Airflow Optimised Cooling Fan

Ultra premium 120mm case cooling fan, featuring advanced structure design derived from the automobile industry. IP68 rated water and dust proof.

Product Code: AK-FN110



Where to Buy 

[OVERVIEW](#)[SPECIFICATION](#)[REVIEWS](#)[SUPPORT](#)[RELATED PRODUCTS](#)

General Information

-

Application	Case, Industrial application
Dimension	120 x 120 x 25 mm
Bearing	Two Ball Bearing
Speed	0 - 2000 RPM
Max Airflow	97.02 CFM
Max Static Pressure	3.59 mm-H2O
Sound Level	7.1 - 31.7 dB(A)
Rated Voltage for Fan	12V DC
Rated Current for Fan	0.16 A
Fan Connector	4-Pin PWM
Fan Life	80,000 hours
Warranty	2 years
Product Code	AK-FN110



AKASA (@akasa_tech)



DISCOVER

About Akasa
Where to Buy
Press Room

SUPPORT

Legacy Products
Contact Us
Terms and Privacy

STAY UP TO DATE!

Subscribe now for free alerts on newly added products, exclusive deals and more.

