



| REV. | DATE     | DESCRIPTION     |
|------|----------|-----------------|
| NC   | 09/19/07 | INITIAL RELEASE |
|      |          |                 |



|   |             |             |         |     |                                                                                                                                        |           |        |                      |  |                                                             |               |      |    |      |   |       |    |
|---|-------------|-------------|---------|-----|----------------------------------------------------------------------------------------------------------------------------------------|-----------|--------|----------------------|--|-------------------------------------------------------------|---------------|------|----|------|---|-------|----|
|   |             |             |         |     | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.             | APPROVALS |        | DATE                 |  | Amphenol Connex                                             |               |      |    |      |   |       |    |
| 8 |             |             |         |     |                                                                                                                                        | DRAWN     | G.R.S. | 09/19/07             |  |                                                             |               |      |    |      |   |       |    |
| 7 |             |             |         |     | UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br>0.5 – 8mm ± 0.20mm<br>8 – 30mm ± 0.40mm<br>30 – 120mm ± 0.50mm           | CHECKED   |        |                      |  | PART DESCRIPTION<br><br>MINI 75 OHM SMB R/A P.C. MOUNT PLUG |               |      |    |      |   |       |    |
| 6 |             |             |         |     |                                                                                                                                        | ISSUED    |        |                      |  |                                                             |               |      |    |      |   |       |    |
| 5 |             |             |         |     | UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br>.020 – .315 = ± 0.007”<br>.315 – 1.180 = ± 0.015”<br>1.180 – 4.724 = ± 0.020” | SHEET     |        | 1 OF 1               |  | PART NO.<br><br>142142-75                                   |               |      |    |      |   |       |    |
| 4 |             |             |         |     |                                                                                                                                        | CAD FILE  |        | C:/142/142142-75.DWG |  |                                                             |               |      |    |      |   |       |    |
| 3 | CONTACT PIN | BER. COPPER | GOLD    | 1   | DO NOT SCALE DRAWING                                                                                                                   |           |        |                      |  | DWG. NO.                                                    | 142142-75.DWG | REV. | NC | SIZE | A | SCALE | NA |
| 2 | INSULATOR   | TEFLON      | NATURAL | 1   |                                                                                                                                        |           |        |                      |  |                                                             |               |      |    |      |   |       |    |
| 1 | BODY        | BRASS       | GOLD    | 1   |                                                                                                                                        |           |        |                      |  |                                                             |               |      |    |      |   |       |    |
|   | DESCRIPTION | MATERIAL    | FINISH  | QTY |                                                                                                                                        |           |        |                      |  |                                                             |               |      |    |      |   |       |    |