




REV.	DATE	DESCRIPTION
NC	12/16/98	INITIAL RELEASE



RECOMMENDED CABLE
STRIPPING DIMENSIONS



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	APPROVALS	DATE	 Connector Corporation			
1 BODY	BRASS	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN	12/16/98	TITLE MCX DIRECT SOLDER PLUG (FOR .047" SEMI RIGID CABLE)			
2 INSULATOR	TEFLON	NATURAL		CHECKED		SIZE A			
3 CONTACT PIN	BRASS	GOLD		ISSUED		FSCM NO. 99001			
4 SOLDER BARREL	BRASS	GOLD				DWG. NO. 252156.DWG			
5						REV. NC			
6									
7									
8			DO NOT SCALE DRAWING			SCALE	NA	PART NO.	1 OF 1