

Switching probe SKS-415 002 230 A 2302 E

Item SKS-415-0093



ingun[®]

Partner for Future Technology

General data

Product group	Switching probes
Sub-product group	SKS (pressed-in)
Series	SKS-415 E quick-exchange / plug system
Grid	3.5 mm [137 mil]
Contacting from	Presence check
Magnetic	Yes
Installation type	Plug-in
Quick-exchange system	Yes
Type of test probe connection	Plug
Adjustable installation height	No
Non-rotating	No
Compatible connector(s)	SE-415 KS, SE-502
Compatible receptacle(s)	KS-113 23, KS-415 S
Min. temperature	- 40 °C [- 104 °F]
Max. temperature	+ 80 °C [+ 176 °F]
RoHS-compliant	RoHS-3;6c

Electrical data


Current load capacity / rated current	5 A
Typical resistance (Ri)	<100 mOhm

Mechanical data

Total length	43.3 mm [1.70 in]
Barrel diameter	2.65 mm [.104 in]
Maximum stroke	5.2 mm [.204 in]
Spring pre-load	0.5 N [1.79 ozf]
Collar height	.02
Switch path	1.7 mm [.066 in]
Switching point	8.5 mm [.334 in]
Spring force at switching point	0.9 N [3.23 ozf]

Tip style data

Tip style	002 flat, contact surface insulated
Tip diameter	2.3 mm [.090 in]
Tip style surface	A gold
Tip style material	0 plastic



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 12/23 EN

Learn more about
Test probes

