



Qoltec DIN rail power supply | 40W | 24V | 1.67A | White | Slim

Product code: 50911

DIN rail power supplies are industrial power supplies that in addition to a sufficiently high degree of protection ensuring protection against external conditions, also have high power and efficiency parameters.

MULTIDISCIPLINARY APPLICATION TO HELP YOU MAKE THE RIGHT CHOICE

Qoltec DIN rail power supplies are a useful component for automation systems, machine control, lighting technology and industrial electronics where the size of the power equipment is important and adaptation to limited space is essential.

COMPACT DIMENSIONS

The SLIM version makes it easier to organize the space for mounting the power supply - its small size will allow for trouble-free installation, and the ergonomic shape will easily fit into the selected electrical cabinet.

MATCH YOUR MODEL

You don't know which power supply to choose? It's easy:

It is essential to calculate the power consumption of all devices it supports. The sum will allow determining the minimum power that will ensure the operation of all components in the system powered by a specific DIN power supply. It is worth remembering that when choosing a power supply, provide a reserve of approx. 10-15% of power for the safe functioning of the equipment connected to it.

WE CARE ABOUT YOUR SAFETY

DIN rail power supplies are made of the highest quality materials to provide you with reliable power in any situation. Additionally, it has protection against:

- **overvoltage protection** against too low or too high input voltage,
- **overload protection** is protection against overload of each power line
- **short circuits** is a protection against short circuits in the power supply circuit

BE MORE ECO

Our company makes every effort to protect the environment, thus the presented model is packed in a biodegradable box.

TRUST CONFIRMED BY WARRANTY

Do you care about the high quality of the product you buy? Our proposals will meet your expectations. Each of the DIN power supplies we offer is covered by a 24-month warranty valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Input voltage adjustment range	23.5 - 29 V dc
Usable power	40 W
Input voltage	220 - 240 V
Frequency	50 - 60 Hz
Output current	1.67 A
Output voltage	24 V
Security	- overvoltage protection - overload protection - short-circuit protection
Efficiency	86%
IP rating	IP 20
Working temperature	-30 C ~ +70
Additional information	For use only with a device conforming to the specifications indicated in the device's specification Mounting on DIN rail TS35 / 7.5 or 15 Built-in active DC OK signal
Color	White
Certifications	CE
Dimensions	100 x 40 x 90 mm
Package depth / length [mm]	104
Package width [mm]	43
Package height [mm]	110
Package contents	DIN rail power supply
Net weight [kg]	0.2560
Gross weight [kg]	0.2750
Warranty	24 months
EAN code	5901878509112