



Qoltec LED Driver IP20 | 60W | 12V | 5A | Slim case

Product code: 50962

The LED switching power supply is a device characterized by stability and operational reliability. The thin design of the housing allows the use of the power supply in a place with limited access, and thanks to the highest quality components, the power supply meets the expectations of the most demanding customers.

It is designed to power LED strips, modules, panels, LED tapes, bulbs and many other electronic parts powered by 12V.

Reliable LED supply

Are you looking for a reliable way to power the LED strip in your home? Or maybe in your company LED modules are an important element of the lighting installation? If so, you've come to the right place. The Qoltec brand has prepared a **wide selection of modular power supplies** for you, which are perfect for both home and office work. Thanks to their differentiation in terms of power, you can easily choose the model that suits you.

Safe solution

Our device is equipped with modern technologies ensuring protection against:

- **overvoltage** - protects against too low or too high voltage,
- **overloads** - protects against power line overload,
- **short circuits** - protects against short circuits in the supply circuit

Confidence confirmed by a warranty

You value the quality of purchased equipment so our projects and solutions are focused on **meeting your expectations**. Each modular power supply is covered by **24 months warranty**.

Technical data

Producer	Qoltec
Usable power	60 W
Input voltage	220 V ~ 240 V
Output voltage	12 V
Output current	5 A
Safety	Overload protection Overvoltage protection Short-circuit protection
IP Rating	IP 20
Efficiency	80%
Overload	Larger than 105% of capacity restoration after abnormality removed
Additional information	Switching power supply in a metal housing, converts 230V alternating voltage into 12V DC. It is intended for indoor use. Made of electronic components placed on a printed circuit board in a metal housing.
Working temperature	-20 C ~ +60 C
Storage temperature	-40 C ~ +80 C
Dimensions	40 x 35 x 160 mm
Net weight	0,1720 kg
Gross weight	0,1900 kg
Warranty	24 months
Package size	37 x 45 x 166 mm
EAN code	5901878509624