

DIGITUS DisplayPort Connection Cable

AK-340106-010-S
EAN 4016032450320



DisplayPort connection cable, DP M/M, 1.0m,w/lock, UHD 8K, Vers. 1.3/1.4, bl

With this cable standard, this DisplayPort cable supports all of today's requirements - from the playback of high-resolution UHD 8K content through 8-channel audio transmission to the support of HDCP and DPCP encryptions. Mirror your laptop desktop on a large monitor or extend your desktop with another DisplayPort display. This high-quality cable allows rapid data transfer without jerking, even in demanding graphics applications or games. Gold-plated contacts and double shielding of the cable ensure maximum conductivity and trouble-free transmission.

Ideal for CAD/CAM, GIS, 3D modeling, real time simulation, and more.

- Transmission Rate: up to 32,4 GBit/s
- Support up to 4K/2K@120Hz (Ultra HD) resolution
- Support up to 5K@60Hz (Ultra HD) resolution

- Support up to 8K@30Hz (Ultra HD) resolution
- Supported Video Resolution: 7680 x 4320 dpi; 5120 x 2880 dpi; 3840 x 2160 dpi
- Color depth: 24bit RGB
- Support of 1-8 audio channels for audio transmission
- Audio sampling rate: 32-192 kHz by max. bitrate of 4.608 kB/s
- Support of HDCP and DPCP
- Plug & Play installation
- Color cable: black
- Connector 1: DP, plug
- Connector 2: DP, plug
- Connector surface: nickel-plated
- DisplayPort standard: DisplayPort 1.4
- HDTV Resolution max.: 7680 × 4320 Pixel, 60Hz
- HDTV Standard: Ultra HD 8K
- Length: 1 m
- AOC - Active Optical Cable: no

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	100	8.00	50.00	33.00	22.00	36,300.00
Packaging Unit Inside	10	0.80	2.00	14.00	22.00	616.00
Packaging Unit Single	1	0.08	22.00	14.00	2.50	770.00
Net single without Packaging	1	0.07	22.00	14.00	2.50	770.00

More images:



