

DIGITUS DisplayPort Adapter Cable

AK-340306-020-S
EAN 4016032328537



DisplayPort adapter cable, DP - DVI (24+1) M/M, 2.0m, w/interlock, DP 1.1a compatible, bl

This digital HD cable converts DisplayPort signals to DVI signals and is ideal to connect DisplayPort devices to your HD TV, beamer or monitor with DVI interface.

Perfect for video streams, gaming or extending the workplace

- Support up to 1080p with 60Hz
- Copper wire, foil and braid shielding for robustness and reliable connection
- Plug and play, no additional driver needed
- Supported transmission modes: RBR, HBR, HBR2
- Maximal bandwidth: 10,8 Gbps
- HBR-Version/transfer mode: HBR1 (2,70 Gbit/s per lane)

- HDCP-Version: HDCP 1.3
- Assortment: DisplayPort Cables
- Color cable: black
- Color connector: black
- Connector 1: DP, plug
- Connector 2: DVI-D, (24+1), plug
- Connector surface: nickel-plated
- DisplayPort standard: DisplayPort 1.1a
- HDTV Resolution max.: 1920 x 1080 Pixel, 60Hz
- HDTV Standard: Full HD
- Hoods: molded
- Interlock: Snap fastener
- Length: 2 m
- AOC - Active Optical Cable: no

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	50	6.50	28.00	34.00	45.00	42,840.00
Packaging Unit Inside	5	0.65	22.00	15.00	2.00	660.00
Packaging Unit Single	1	0.13	22.00	15.00	2.00	660.00
Net single without Packaging	1	0.12	22.00	15.00	2.00	660.00

More images:



