

DIGITUS 8K HDMI Ultra High Speed Connection Cable

DB-330200-030-S
EAN 4016032481225



8K PREMIUM HDMI 2.1 Cable 3m Aluminum Housing, Gold plated, Support 8K/60HZ

With this cable standard, the ultra high speed HDMI cable supports all current requirements – from the transmission of high-resolution UHD 8K content, two-way audio transmission (ARC) and control of HDMI devices via CEC. Internet applications can also be used without the additional need to connect an Ethernet cable (HEC). Lip Sync means that delayed lip movement is a thing of the past. This cable can also be used to transmit up to 32 audio channels and enjoy image output in 21:9 CinemaScope format. Get more out of your Blu-ray player, gaming console or HD streaming portal. Gold-plated contacts and triple shielding of the cable ensure maximum conductivity and interference-free transmission. Also supports 4K 3D in 50/60 Hz.

The Digitus® 8K Ultra High Speed Connection Cable already meets the requirements for future high-definition devices (TV, projector, monitor) of the next generation with higher resolutions, higher data rates and higher refresh rates.

- Resolution: 7680 x 4320p / 60 Hz (UHD-2)
- Supports 8K 3D
- Data transfer rate up to 48 Gbps - Zero frame delay
- Supports up to 120Hz at 4K & Full HD (1080p)
- Supports BT.2020 with 10, 12 and 16 Bit per color component
- Subsampling: YUV 4:4:4
- HDCP version: 2.2
- HDMI® version: 2.1
- Supported color depth: 48 Bit Deep Color
- Supports HDR
- Supports enhanced Audio Return Channel (eARC)
- Supports Consumer Electronic Control (CEC)
- Supports Lip Sync (audio/video synchronization)
- Multi Stream audio/video support
- Supports EDID 2.0 (device recognition)
- Supports 21:9 Cinemascope
- 32 channel audio support
- Dolby TrueHD capable

- Supports 8-channel LPCM, 192 kHz, 24-bit audio capability
- Supports DTS-HD Master Audio bitstream
- Supports Super Audio CD (DSD)
- Supports DVD audio
- Supports Blu-ray Disc and HD DVD audio and video
- Latency: Zero frame delay
- Bending radius: 20 mm
- OM version: OM3
- Operating temperature: -20 ~60°C
- Operating humidity: 0 - 95% RH
- Power consumption: 400 mW max.
- Supports DVI Version 1.0 (in conjunction with adapters)
- Supports DVI Version 1.0 (in conjunction with adapters)
- Connection 1: HDMI Type A, plug
- Connection 2: HDMI Type A, plug
- Cable color: black
- Hood: Aluminum housing
- HDMI standard: Ultra High Speed HDMI
- Max. HDTV resolution: 7680 x 4320 pixels, 60Hz
- HDTV standard: Ultra HD 8K
- Contact surface: gold-plated
- Length: 3 m □ AOC - Active Optic Cable: no □ Shielding: double shielding
- Color cable: black
- Connector 1: HDMI type A, plug
- Connector 2: HDMI type A, plug
- Connector surface: gold-plated
- Ferrite filter: none
- HDMI Standard: Ultra High Speed HDMI
- HDTV Resolution max.: 7680 x 4320 Pixel, 60Hz
- HDTV Standard: Ultra HD 8K
- Length: 3 m
- AOC - Active Optical Cable: no

Package contents

- 1x 8K HDMI Ultra High Speed Connection Cable (3 m)

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	30	6.39	33.00	49.00	21.00	33,957.00
Packaging Unit Inside	10	2.13	42.00	23.50	15.00	14,805.00
Packaging Unit Single	1	0.21	22.50	13.00	4.00	1,170.00
Net single without Packaging	1	0.19	22.50	13.00	4.00	1,170.00

More images:

