

DIGITUS 8K DisplayPort Connection Cable Version 1.4

DB-340201-020-S
EAN 4016032481010



PREMIUM DP1.4 DP to DP 8K/60hz,2m Aluminum Housing ,Gold plated, Support 8K/60Hz

With this cable standard, the DisplayPort cable supports all current requirements – from the transmission of high-resolution UHD 8K content, 8-channel audio transmission and support of HDCP and DPCP encryption. Mirror your notebook desktop onto a large monitor or expand your desktop with an additional display using DisplayPort. High-speed data transfer is possible with this high-quality cable, no judder even during the most demanding graphics applications or games. Gold-plated contacts and double shielding of the cable ensure maximum conductivity and interference-free transmission.

The Digitus® 8K DisplayPort Connection Cable Version 1.4 already meets the requirements for future high-definition devices (TV, projector, monitor) of the next generation. The ultimate 8K experience with Ultra-HD II resolutions of up to 7680 x 4320

- Resolution: 7680 x 4320p / 60 Hz (UHD-2)
- Supports 8K 3D
- Data transfer rate of up to 32.4 Gbps (max. bandwidth)
- Supports up to 120Hz at 4K & Full HD (1080p)
- Subsampling: YUV 4:4:4
- HDCP version: 2.2
- DisplayPort™ version: 1.4
- Supported color depth: 16 Bit Deep Color
- Supports HDR
- Supports Consumer Electronic Control (CEC)
- Supports Lip Sync (audio/video synchronization)
- Supports stereoscopic 3D video
- Supports Display Stream Compression 1.2 (DSC)
- Supports EDID 2.0 (device recognition)
- Supports DVI Version 1.0 (in conjunction with adapters)
- Supports forward error correction (FEC)
- Multi Stream audio/video support
- Supports 21:9 Cinemascope
- 32 channel audio support

- Dolby TrueHD capable
- Supports 8-channel LPCM, 192 kHz, 24-bit audio capability
- Supports DTS-HD Master Audio bitstream
- Supports Super Audio CD (DSD)
- Supports DVD audio
- Supports Blu-ray Disc and HD DVD audio and video
- Cable diameter: 6.8 mm
- OM version: OM3
- Operating temperature: -20 ~ 60°C
- Operating humidity: 0 - 95% RH
- Connection 1: DP, Plug
- Connection 2: DP, Plug
- Locking mechanism: Snap-in fastening
- Locking mechanism: Snap-in fastening
- AWG: 30
- DisplayPort standard: DisplayPort 1.4
- Cable color: black
- Hood: Aluminum housing
- HDTV standard: Ultra HD 8K
- Contact surface: gold-plated □ Length: 2 m □ AOC - Active Optic Cable: no □ Shielding: double shielding
- Color cable: black
- Connector 1: DP, plug
- Connector 2: DP, plug
- Connector surface: gold-plated
- DisplayPort standard: DisplayPort 1.4
- Ferrite filter: none
- HDTV Standard: Ultra HD 8K
- Interlock: none
- Length: 2 m
- AOC - Active Optic Cable: no
- Shielding: Double shielding

Package contents

- 8K DisplayPort Connection Cable Version 1.4 (2m)

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	50	7.50	36.00	39.00	25.00	35,100.00
Packaging Unit Inside	5	0.75	26.00	20.00	7.00	3,640.00
Packaging Unit Single	1	0.15	16.00	16.00	2.00	512.00
Net single without Packaging	1	0.15	16.00	16.00	2.00	512.00

More images:

