

DIGITUS USB Type-C™ connection cable, Type-C™ to C

AK-300138-018-S
EAN 4016032368946



USB Type-C connection cable, type C to C M/M, 1.8m, 3A, 480MB, 2.0 Version, bl

For connection of external USB-C™ devices (e.g. PC, Tablet or Smartphone) to the USB-C™ Host (e.g. PC, Notebook).
Data transfer rate up to 480 Mbps (High-Speed).

For superfast synchronising and charging

- Copper wire, foil and braid shielding for robustness and reliable connection
- Data transfer rate up to 5 Gb/s (SuperSpeed)
- Power supply up to 5V/3A and 15W
- Support of USB PD (Power Delivery) specification
- Type-C™ connector can be used in both directions

- Assortment: USB Cables
- AWG: 24/28
- Color cable: black
- Color connector: black
- Connector 1: USB C, plug
- Connector 2: USB C, plug
- Connector surface: nickel-plated
- Hoods: molded
- Wire material: CU
- Length: 1.8 m
- Shielding: Double shielding
- USB-C Products: yes

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	400	8.00	50.00	32.00	21.00	33,600.00
Packaging Unit Inside	10	0.20	30.00	20.00	1.40	840.00
Packaging Unit Single	1	0.02	9.00	9.00	0.62	50.22
Net single without Packaging	1	0.02	9.00	9.00	0.62	50.22

More images:



