

USB Type-C 9-in-1 multi-port adapter (Hub3.0 + HDMI + DisplayPort + VGA + PD + LAN + stereo audio)

A-CM-COMBO9-02

- 9-in-1: USB 3 hub, 4K HDMI, DisplayPort and Full HD VGA video, stereo audio, Gigabit LAN port and USB Type-C PD charge support
- Fast Gigabit networking and Superspeed USB 3.0 data transfer via USB hub
- Practical card reader, video and audio outputs
- Plug & Play



Features

- 3-port USB 3.1 Gen 1 (5 Gbps) hub
- HDMI port with UHD 4K @30 Hz support
- DisplayPort port with UHD 4K @30 Hz support
- VGA Full HD video port
- Audio stereo 3.5 mm output
- 87 W USB Type-C Power Delivery 3.0 port
- 10/100/1000 Mbps Gigabit LAN port
- Durable premium style metal housing

Packaging

Q'ty in crtn, pcs	30
Crtn volume, CUM	0.055883
Crtn weight, kgs	8.28
Individual package size LxWxH:	335x128x25 mm
Carton size LxWxH:	470x410x290 mm
Country of origin	CN
Barcode	8716309124331
Customs code	8544429090

Package contents

Adapter
USB Type-C cable, 30 cm

Specifications

Input: USB 3.x Type-C male; 30 cm cable length
USB 3.1 Gen 1 output (5 Gbps): 3 pcs x Type-A (female, blue)

HDMI output: Type-A (female), max. resolution: 4K @ 30 Hz
DisplayPort output: female, max. resolution: 4K @ 30 Hz

USB Type-C PD port: Max. PD 2.0 up to 87 W

LAN: Gigabit, RJ45 port

VGA 1920 x 1080 @60 Hz video and 3.5 mm stereo audio sockets

Power consumption: 5 V DC, up to 0.2 A

Dimensions: 201 x 74 x 20 mm

Net weight: 0.193 kg

System requirements

The USB Type-C video source device must support DisplayPort™ Alt Mode

Certificates

