

DIGITUS DisplayPort extension cable, DP

AK-340200-020-S
EAN 4016032289142



DisplayPort extension cable, DP M/F, 2.0m, w/interlock, DP 1.2 conform, bl

This high performance HD digital audio and video cable used for extension of existing DisplayPort connections between graphic card and Monitor, for example.

Transports High Performance - HD audio/video signals over longer distances

- Support up to 1080p with 60Hz
- Supported Video Resolution: 4K (3840x2160) @ 60 Hz, Full HD (1920x1080) @ 120 Hz
- Supported transmission modes: RBR, HBR, HBR2
- Maximal bandwidth: 21,6 Gbps
- HBR-Version/transfer mode: HBR2 (5,40 Gbit/s per lane)
- HDCP-Version: HDCP 1.3
- Assortment: DisplayPort Cables

- AWG: 28
- Color cable: black
- Color connector: black
- Connector 1: DP, plug
- Connector 2: DP, jack
- Connector surface: nickel-plated
- DisplayPort standard: DisplayPort 1.2
- Ferrite filter: none
- HDTV Standard: Ultra HD 4K
- Hoods: molded
- Interlock: Snap fastener
- Packaging: Polybag
- Wire material: CU
- Length: 2 m
- AOC - Active Optical Cable: no
- Shielding: Double shielding

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	70	12.00	50.00	32.00	22.00	35,200.00
Packaging Unit Inside	1	0.17	22.00	15.00	2.50	825.00
Packaging Unit Single	1	0.17	22.00	15.00	2.50	825.00
Net single without Packaging	1	0.16	22.00	15.00	2.50	825.00

More images:



