

LED T8 tube 24W, 2400lm, 6000K, 150cm

Marka: **Virone** | Symbol: **SW-8/150CM/6** | Ean: **5904988905331**




PRODUCT DESCRIPTION

T8 LED tube 150 cm long is a light source with a cold color temperature (6000K) and power of 24W, which will come to the aid of all those who look for modern and efficient lighting systems. They successfully replace traditional gas fluorescent lamps, both in industrial and home lighting. Customers looking for savings and for a durable light source are increasingly reaching for LED linear fluorescent lamps. Classic in shape, economical in use - LED linear fluorescent lamps emit a luminous flux - depending on the selected model - from 900 to 2400 lm. Such light sources are used wherever intense lighting is needed, immediately after switching on the device.

They will be suitable in storage and exhibition halls, shopping malls as well as in a home workshop. Linear fluorescent lamp available in various power types and sizes.

TECHNICAL DATA

General information:

Lamp power:	24 W
Light source:	LED
Lamp voltage:	230 V
Luminous flux:	2400 lm
Colour temperature:	6000K
Socket:	G13/T8
Glass colour:	Matt
Energy efficiency class:	F
Dimmable:	No
Durability:	30000h
Weighted energy consumption in 1000 hours:	24 kWh
Colour rendering index:	80
Light distribution angle:	270°
Activation cycle:	15000
Shockproof:	No
With motion sensor:	No
Total length:	1500 mm
Diameter:	26 mm

