




Schaltplan / Pin Out


P1	P2
1	1
2	2
3	3
4	4



P1



P2



USB 2.0 Hi-Speed-Adapter

Anschlüsse: USB 2.0 Stecker (Typ B)
 USB 2.0 Buchse (Typ A)
 Leiterwiderstand: 5 Ω
 Isolationswiderstand: 5 M Ω @ 300 V ===
 Kontaktmaterial: vernickelt

USB 2.0 Hi-Speed Adapter

Connections: USB 2.0 plug (type B)
 USB 2.0 socket (type A)
 Conductor resistance: 5 Ω
 Insulation resistance: 5 M Ω @ 300 V ===
 Contact material: nickel plated

Änderungen

Datum	Name	gez.:	Datum	Name
		gepr.:	24.01.2024	ir
		Norm:	24.01.2024	ZK

Bezeichnung

USB ADAP A-F/B-M

Zeichnungs-Nr.:

50291



Blatt

1

von

1

Änderungen vorbehalten / Subject to change