

SOPOT LED 12W, ceiling light, 1190lm, IP20, 4000K, PVC lampshade

Marka: **ADVITI** | Symbol: **AD-PL-6459WLZM4** | Ean: **5908254840388**

Adviti



PRODUCT DESCRIPTION

The ADVITI ceiling light family offers a wide range of models and sizes. Wall and ceiling luminaires are an indispensable part of any room's furnishings, so it is worth ensuring that they serve us efficiently and impressively for a long time.

The product is available in three power options: 12W, 18W, 24W.

You can easily compile matching, unpretentious and elegant lighting in this category - for both indoors and outdoors, for your home, business or flat. Functional and coherent arrangements can be created by selecting lamps from several available series, each with specific strengths and characteristics.

SOPOT, is a 12 W LED ceiling light with a neutral colour of light (4000K) and a luminous flux of 1190lm. The luminaire is convenient even for self-assembly.

SOPOT is also a universal lamp for various tasks - it will work well in a corridor, staircase or pantry, and can be mounted both on the wall and on the ceiling. The IP20 protection level will be quite sufficient in such rooms.

The round, white lampshade made of milky PVC will aesthetically blend in with both avant-garde interior design and simple minimalist furnishings such as an office common area. This form of lighting will prove its worth wherever universality and functionality are important.

TECHNICAL DATA

General information:

Nominal voltage:	230 V
Lamp type:	LED, wymienne
Suitable for lamp power:	12 W
Rated luminous flux according to IEC 62722-2-1:	1190lm
Luminaire efficacy:	99lm/W
With light source:	tak
Colour temperature:	4000K
Beam angle:	120
Rated life time L70/B50 at 25 °C:	30000
Colour rendering index CRI:	80
:	12 W
:	Nie
Energy efficiency class of the built-in lamp:	F
Colour of light:	Neutralny biały
Power factor:	0.7
Flickering value Pst LM:	0.5

Stroboscope effect value SVM:	0.4
Degree of protection (IP):	20
Impact strength:	IK05
Protection class:	I
Suitable for wall mounting:	tak
Suitable for suspended mounting:	nie
Suitable for ceiling mounting:	tak
Suitable for built-in mounting:	nie
Suitable for surface mounting:	tak
Suitable for light line configuration:	nie
Material housing:	metal
Material cover:	PVC
With movement sensor:	nie
With light sensor:	nie
Width:	260
Height/depth:	58
Length:	260
Voltage type:	AC
Exchangeable control gear:	tak

