

Marka: **ADVITI** | Symbol: **AD-PL-6459WLZMM4** | Ean: **5908254840395**

**Adviti**



## PRODUCT DESCRIPTION

## TECHNICAL DATA

## General information:

|                                                      |                 |
|------------------------------------------------------|-----------------|
| Nominal voltage [V]:                                 | 230 V           |
| Lamp type:                                           | LED, wymienne   |
| Suitable for lamp power [W]:                         | 12 W            |
| Rated luminous flux according to IEC 62722-2-1 [lm]: | 1190lm          |
| Luminaire efficacy [lm/W]:                           | 99lm/W          |
| With light source:                                   | tak             |
| Colour temperature [K]:                              | 4000K           |
| Beam angle:                                          | 120             |
| Rated life time L70/B50 at 25 °C [h]:                | 30000           |
| Colour rendering index CRI:                          | 80              |
| :                                                    | 12 W            |
| :                                                    | Nie             |
| Energy efficiency class of the built-in lamp:        | F               |
| Colour of light:                                     | Neutralny biały |
| Power factor:                                        | 0.7             |
| Flickering value Pst LM:                             | 0.5             |
| Stroboscope effect value SVM:                        | 0.4             |
| Degree of protection (IP):                           | 20              |
| Impact strength:                                     | IK05            |
| Protection class:                                    | I               |
| Suitable for wall mounting:                          | tak             |
| Suitable for suspended mounting:                     | nie             |
| Suitable for ceiling mounting:                       | tak             |
| Suitable for built-in mounting:                      | nie             |
| Suitable for surface mounting:                       | tak             |
| Suitable for light line configuration:               | nie             |
| Material housing:                                    | metal           |
| Material cover:                                      | PVC             |

|                              |           |
|------------------------------|-----------|
| With movement sensor:        | tak       |
| Sensor type:                 | microwave |
| Detection range:             | 3-7m      |
| Adjustable daylight sensor : | 15Lux     |
| Adjustable time setting :    | 40s       |
| Width [mm]:                  | 260       |
| Height/depth [mm]:           | 58        |
| Length [mm]:                 | 260       |
| Voltage type:                | AC        |
| Exchangeable control gear:   | tak       |



