

Marka: **ADVITI** | Symbol: **AD-PL-6460WLZMM4** | Ean: **5908254840418**

Adviti



PRODUCT DESCRIPTION

TECHNICAL DATA

General information:

Nominal voltage [V]:	230 V
Lamp type:	LED, wymienne
Suitable for lamp power [W]:	18 W
Rated luminous flux according to IEC 62722-2-1 [lm]:	1880lm
Luminaire efficacy [lm/W]:	104lm/W
With light source:	tak
Colour temperature [K]:	4000K
Beam angle:	120
Rated life time L70/B50 at 25 °C [h]:	30000
Colour rendering index CRI:	80
:	18 W
:	Nie
Energy efficiency class of the built-in lamp:	F
Colour of light:	Neutralny biały
Power factor:	0.7
Flickering value Pst LM:	0.5
Stroboscope effect value SVM:	0.4
Degree of protection (IP):	20
Impact strength:	IK05
Protection class:	I
Suitable for wall mounting:	tak
Suitable for suspended mounting:	nie
Suitable for ceiling mounting:	tak
Suitable for built-in mounting:	nie
Suitable for surface mounting:	tak
Suitable for light line configuration:	nie
Material housing:	metal
Material cover:	PVC

With movement sensor:	tak
Sensor type:	microwave
Detection range:	3-7m
Adjustable daylight sensor :	15Lux
Adjustable time setting :	40s
Width [mm]:	350
Height/depth [mm]:	62
Length [mm]:	350
Voltage type:	AC
Exchangeable control gear:	tak