

## JANTAR LED 18W, ceiling light, 1880lm, IP54, 4000K, PC lampshade

Marka: **ADVITI** | Symbol: **AD-PL-6468WLPM4** | Ean: **5908254840814**

**Adviti**



### PRODUCT DESCRIPTION

JANTAR LED 18W is a wall and ceiling light, which is characterised not only by its high functionality or resistance, but also by its aesthetic appearance.

The device has 18W LEDs that generate a bright and even luminous flux of 1880 lm. This brightness is optimal both for use in domestic interiors and in various public spaces such as offices, hotels, schools or shops.

The color temperature of the plafond is 4000K, which means a neutral white light colour. This is ideal for rooms where good lighting is required while maintaining the natural color of the walls and furniture.

The JANTAR LED 18W ceiling light has a high protection level IP54, which provides protection against dust, moisture and even water. As a result, the product can be used in a variety of locations, including bathrooms and corridors. In addition, the high impact resistance (IK08) ensures safety when using the product.

The simple, classic design makes this plafond very versatile and can be used in different types of rooms and decor styles. Being able to choose the size that suits your needs allows you to create a consistent lighting arrangement throughout your home or office.

The product is available in three power options: 18W, 24W, 30W and a version with a motion sensor.

## TECHNICAL DATA

### General information:

|                                                 |                 |
|-------------------------------------------------|-----------------|
| Nominal voltage:                                | 230 V           |
| Lamp type:                                      | LED, wymienne   |
| Suitable for lamp power:                        | 18 W            |
| Rated luminous flux according to IEC 62722-2-1: | 1880lm          |
| Luminaire efficacy:                             | 104lm/W         |
| With light source:                              | tak             |
| Colour temperature:                             | 4000K           |
| Beam angle:                                     | 120             |
| Rated life time L70/B50 at 25 °C:               | 30000           |
| Colour rendering index CRI:                     | 80              |
| :                                               | 18 W            |
| :                                               | Nie             |
| Energy efficiency class of the built-in lamp:   | F               |
| Colour of light:                                | Neutralny biały |
| Power factor:                                   | 0.9             |
| Flickering value Pst LM:                        | 0.5             |
| Stroboscope effect value SVM:                   | 0.4             |

|                                        |       |
|----------------------------------------|-------|
| Degree of protection (IP):             | 54    |
| Impact strength:                       | IK08  |
| Protection class:                      | II    |
| Suitable for wall mounting:            | tak   |
| Suitable for suspended mounting:       | nie   |
| Suitable for ceiling mounting:         | tak   |
| Suitable for built-in mounting:        | nie   |
| Suitable for surface mounting:         | tak   |
| Suitable for light line configuration: | nie   |
| Material housing:                      | metal |
| Material cover:                        | PC    |
| With movement sensor:                  | nie   |
| With light sensor:                     | nie   |
| Width:                                 | 220   |
| Height/depth:                          | 51    |
| Length:                                | 220   |
| Voltage type:                          | AC    |
| Exchangeable control gear:             | tak   |

