

JANTAR LED 24W, ceiling light, 2565lm, IP54, 4000K, PC lampshade

Marka: **ADVITI** | Symbol: **AD-PL-6469WLPM4** | Ean: **5908254840838**

Adviti



PRODUCT DESCRIPTION

JANTAR LED 24W is a wall and ceiling light, which is characterised not only by its high functionality or resistance, but also by its aesthetic appearance.

The device has 24W LEDs that generate a bright and even luminous flux of 2565 lm. This brightness is optimal both for use in domestic interiors and in various public spaces such as offices, hotels, schools or shops.

The color temperature of the plafond is 4000K, which means a neutral white light colour. This is ideal for rooms where good lighting is required while maintaining the natural color of the walls and furniture.

The JANTAR LED 24W ceiling light has a high protection level IP54, which provides protection against dust, moisture and even water. As a result, the product can be used in a variety of locations, including bathrooms and corridors. In addition, the high impact resistance (IK08) ensures safety when using the product.

The simple, classic design makes this plafond very versatile and can be used in different types of rooms and decor styles. Being able to choose the size that suits your needs allows you to create a consistent lighting arrangement throughout your home or office.

The product is available in three power options: 18W, 24W, 30W and a version with a motion sensor.

TECHNICAL DATA

General information:

Nominal voltage:	230 V
Lamp type:	LED, wymienne
Suitable for lamp power:	24 W
Rated luminous flux according to IEC 62722-2-1:	2565lm
Luminaire efficacy:	106lm/W
With light source:	tak
Colour temperature:	4000K
Beam angle:	120
Rated life time L70/B50 at 25 °C:	30000
Colour rendering index CRI:	80
:	24 W
:	Nie
Energy efficiency class of the built-in lamp:	F
Colour of light:	Neutralny biały
Power factor:	0.9
Flickering value Pst LM:	0.5
Stroboscope effect value SVM:	0.4

Degree of protection (IP):	54
Impact strength:	IK08
Protection class:	II
Suitable for wall mounting:	tak
Suitable for suspended mounting:	nie
Suitable for ceiling mounting:	tak
Suitable for built-in mounting:	nie
Suitable for surface mounting:	tak
Suitable for light line configuration:	nie
Material housing:	metal
Material cover:	PC
With movement sensor:	nie
With light sensor:	nie
Width:	280
Height/depth:	51
Length:	280
Voltage type:	AC
Exchangeable control gear:	tak