




5-100C-1 / 5-450C-2

Adjustable Wrenches Chrome Plated



PRODUCT DETAILS

- Jaw will not fall out even at maximum wrench opening
- Laser scale in mm for pre-adjusting and accurate measurement
- Parallel jaws at a 15° angle provide a firm grip and good reach
- High-performance alloy steel forged in a single piece
- Chrome plated finish, precision hardened and anti-corrosion treated
- Standards: ISO 6787, DIN 3117, ASME B107.8-2003 and BS 6333
- - 1 retail packaging and -2 industrial packaging



PRODUCT ATTRIBUTES

Product	L	L	A	B	D	E	
5-100C-1	4 in	115 mm	13 mm	13.5 mm	3.5 mm	9 mm	60 g
5-150C-1	6 in	160 mm	20 mm	21 mm	5.5 mm	12 mm	130 g
5-200C-1	8 in	205 mm	24 mm	26 mm	7.5 mm	13.5 mm	250 g
5-250C-1	10 in	260 mm	29 mm	29.5 mm	9 mm	16 mm	405 g
5-300C-1	12 in	310 mm	36 mm	36 mm	11 mm	19 mm	650 g
5-375C-2	15 in	385 mm	43 mm	45 mm	13 mm	24 mm	1230 g
5-450C-2	18 in	465 mm	57 mm	53 mm	15 mm	27.5 mm	2000 g