

Eaton 100NHG000B

Catalog Number: 100NHG000B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 100A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, square-body with knife blade contact, Metal plated copper contact plat



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	100NHG000B
Packing Unit	
Pack	
Case Pack	
Quantity	
3	
60	
Length	
83 mm	
420 mm	
Height	
56 mm	
140 mm	
ERP Name	
SAP-UNITY	
SAP-UNITY	
Product Height	
51 mm	
Product Weight	
119.333 g	
Product Length/Depth	
79 mm	
Product Width	
21 mm	
Gross Weight	
0.392 kg	
8.205 kg	
Volume	
362.544 cm ³	
10584 cm ³	
Width	
78 mm	
180 mm	
EAN	
5027590413169	
5027590363389	

Compliances

CE Marked

Certifications

IEC 60269-1

Electrical data

Amperage Rating

100 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Model Code

NH FUSE 100A

MGL

Fuse size

NH000

SIZE 000 GG

Insulated metal gripping lugs (IMGL)

No

DIN 43620

Product specification

Accessories

Suitable for

Microswitch 170H0236

EBF Vertical fuse rail

EBV Vertical fuse switch-disconnectors

EBH Size 000 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia