

Eaton 100NHG01B

Catalog Number: 100NHG01B

Eaton Bussmann series low voltage NH Fuse, 500V, 100A, 120 kAIC, Combination fuse status indicator, fuse, Class C gL/gG

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	100NHG01B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590363402	36
5027590370202	3
Gross Weight	Length
11 kg	325 mm
0.884 kg	137 mm
Width	Height
290 mm	155 mm
102 mm	68 mm
Volume	ERP Name
14608.75 cm ³	SAP-UNITY
950.232 cm ³	SAP-UNITY
Product Length/Depth	Product Height
135 mm	57.8 mm
Product Width	Product Weight
29.55 mm	270.667 g
Compliances	Certifications
RoHS Compliant	IEC 60269-1
CE Marked	IEC 60269-2
	DIN 43620

Type

fuse

Application

industrial

Utilities, Solar, Wind

Amperage Rating

100 A

Fitted with:

Metal gripping lugs

Fuse size

NH01

Current type

AC

Breaking capacity

120 kA

Frequency rating - max

62 Hz

Frequency rating - min

45 Hz

Rated switching capacity

120 kA

Rated voltage AC

500 V

Class

Class gG/gL

Fuse type

Square body with knife blade contact

Utilization category

gL/gG (cable protection/equipment protection)

Interrupt rating

120 kAIC

Fuse indicator

Combination fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Connection

Blade end

Construction

NH01

Construction size

NH01

Fuse shape

Knife blade contacts

Square body

Voltage type

AC

Suitable for

Microswitch 170H0235

Material

Ceramic body

Quantity

3

Voltage rating

500 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia