

Eaton 125NHG00B

Catalog Number: 125NHG00B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 125A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Metal plated copper contact plate

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	125NHG00B
Packing Unit	
Pack	
Case Pack	
Quantity	
5027590408936	3
5027590363471	72
Gross Weight	Length
0.59 kg	102 mm
14.64 kg	350 mm
Width	Height
80 mm	63 mm
220 mm	215 mm
Volume	ERP Name
514.08 cm ³	SAP-UNITY
16555 cm ³	SAP-UNITY
Product Length/Depth	Product Height
79 mm	58 mm
Product Width	Product Weight
30 mm	182 g

		Compliances	Certifications
		CE Marked	IEC 60269-1
Electrical data		Product specification	
Amperage Rating		Model Code	Fuse size
125 A		NH FUSE 125A 500V GG/GL SIZE 00	NH02
Voltage rating			Insulated metal gripping lugs (IMGL)
500 V			No
Voltage type			
AC			
Breaking capacity			
120 kA			
Frequency rating - min			
45 Hz			
Frequency rating - max			
62 Hz			