

Eaton 125NHG02B

Catalog Number: 125NHG02B

Fuse-link, LV, 125 A, AC 500 V, NH02, gL/gG, IEC, dual indicator, live gripping lugs

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	125NHG02B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590363495	36
5027590408950	3
Gross Weight	Length
16.125 kg	420 mm
1.28 kg	152 mm
Width	Height
320 mm	175 mm
132 mm	76 mm
Volume	ERP Name
23520 cm ³	SAP-UNITY
1524.864 cm ³	SAP-UNITY
Product Length/Depth	Product Height
150 mm	63 mm
Product Width	Product Weight
40 mm	395.333 g
Compliances	Certifications
RoHS Compliant	IEC 60269-1
CE Marked	IEC 60269-2
	DIN 43620

Electrical data

Amperage Rating

125 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

Fuse size

NH00

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

SD00-D Single pole NH Fuse base

TD00-D Tripe pole NH Fuse base

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia