

Eaton 160NHG00B

Catalog Number: 160NHG00B

Eaton Bussmann series low voltage NH Fuse, 160A, 500 V, 120 kAIC, Blade end

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	160NHG00B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590363525	72
5027590191241	3
Gross Weight	Length
14.64 kg	350 mm
0.59 kg	102 mm
Width	Height
220 mm	215 mm
80 mm	63 mm
Volume	ERP Name
16555 cm ³	SAP-UNITY
514.08 cm ³	SAP-UNITY
Product Length/Depth	Product Height
79 mm	58 mm
Product Width	Product Weight
30 mm	182 g
Compliances	Certifications
CE Marked	IEC 60269-1
RoHS Compliant	IEC 60269-2
	DIN 43620

Electrical data

Amperage Rating

160 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

Fuse size

NH00

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

SD00-D Single pole NH Fuse base

TD00-D Tripe pole NH Fuse base

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia