

Eaton 160NHG01B

Catalog Number: 160NHG01B

Eaton Bussmann series low voltage NH Fuse, 160 A, 500 V, 120 kAIC, Blade end

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	160NHG01B
	Packing Unit
	Pack
	Case Pack
EAN	Quantity
5027590191258	3
5027590363532	36
Gross Weight	Length
0.884 kg	137 mm
11 kg	325 mm
Width	Height
102 mm	68 mm
290 mm	155 mm
Volume	ERP Name
950.232 cm ³	SAP-UNITY
14608.75 cm ³	SAP-UNITY
Product Length/Depth	Product Height
135 mm	57.8 mm
Product Width	Product Weight
29.55 mm	270.667 g
Compliances	Certifications
CE Marked	IEC 60269-1
RoHS Compliant	IEC 60269-2
	DIN 43620

Electrical data

Amperage Rating

160 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

Fuse size

NH01

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

Microswitch 170H0235

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia