

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 224A, 120 kAIC, Combination fuse status indicator, fuse, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	224NHG1B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590363686	36
5027590194877	3
Gross Weight	Length
15.199 kg	475 mm
1.222 kg	137 mm
Width	Height
290 mm	155 mm
134 mm	68 mm
Volume	ERP Name
21351.25 cm ³	SAP-UNITY
1248.344 cm ³	SAP-UNITY
Product Length/Depth	Product Height
135 mm	63 mm
Product Width	Product Weight
40 mm	407.3333333 g



Compliances

CE Marked

Certifications

IEC 60269-1

Electrical data

Amperage Rating

224 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

DIN 43620

Fuse size

NH1

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

SD1-D Single pole NH Fuse base

TD1-D Tripe pole NH Fuse base

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia