

Eaton 250NHG02B

Catalog Number: 250NHG02B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 250A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Metal plated copper contact plate



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	250NHG02B
Packing Unit	
Case Pack	
Pack	
Quantity	
36	
3	
Length	
420 mm	
152 mm	
Height	
175 mm	
76 mm	
ERP Name	
SAP-UNITY	
SAP-UNITY	
Product Height	
63 mm	
Product Weight	
395.333 g	

Product Length/Depth	
150 mm	
Product Width	
40 mm	

Compliances
RoHS Compliant

Certifications
IEC 60269-1

Electrical data

Amperage Rating

250 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

DIN 43620

Fuse size

NH02

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

Microswitch BVL50

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia