

Eaton 25NHG000B

Catalog Number: 25NHG000B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 25A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Metal plated copper contact plate, Ceramic body



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	25NHG000B
	Packing Unit
	Pack
	Case Pack
EAN	Quantity
5027590196406	3
5027590363723	60
Gross Weight	Length
0.392 kg	83 mm
8.205 kg	420 mm
Width	Height
78 mm	56 mm
180 mm	140 mm
Volume	ERP Name
362.544 cm ³	SAP-UNITY
10584 cm ³	SAP-UNITY
Product Length/Depth	Product Height
79 mm	51 mm
Product Width	Product Weight
21 mm	131 g

		Compliances	Certifications
		CE Marked	IEC 60269-1
Electrical data		Product specification	
Amperage Rating		Model Code	Fuse size
25 A		NH FUSE 25A 500V SIZE 000 GG MGL	NH01
Voltage rating			Insulated metal gripping lugs (IMGL)
500 V			No
Voltage type			
AC			
Breaking capacity			
120 kA			
Frequency rating - min			
45 Hz			
Frequency rating - max			
62 Hz			