

Eaton 315NHG1B

Catalog Number: 315NHG1B

Fuse-link, LV, 315 A, AC 440 V, NH1, gL/gG, IEC, dual indicator, live gripping lugs

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	315NHG1B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590342810	36
5027590225281	3
Gross Weight	Length
15.199 kg	385 mm
1.273 kg	137 mm
Width	Height
280 mm	175 mm
134 mm	68 mm
Volume	ERP Name
19193.65 cm ³	SAP-UNITY
1248.344 cm ³	SAP-UNITY
Product Length/Depth	Product Height
135 mm	63 mm
Product Width	Product Weight
40 mm	424.3333333 g
Compliances	Certifications
CE Marked	IEC 60269-1
RoHS Compliant	IEC 60269-2
	DIN 43620

Electrical data

Amperage Rating

315 A

Voltage rating

440 V

Voltage type

AC

Breaking capacity

120 kA

Product specification

Fuse size

NH1

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

SD1-D Single pole NH Fuse base

TD1-D Tripe pole NH Fuse base

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Do pobrania

Biuletyny usług serwisowych

Datasheet - 315NHG1B (PL)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia