

Eaton 315NHG2B

Catalog Number: 315NHG2B

Fuse-link, low voltage, 315 A, AC 500 V, NH2, gL/gG, IEC, dual indicator

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	315NHG2B
	Packing Unit
	Pack
	Case Pack
EAN	Quantity
5027590199322	3
5027590364362	24
Gross Weight	Length
1.978 kg	153 mm
16.474 kg	365 mm
Width	Height
172 mm	76 mm
320 mm	165 mm
Volume	ERP Name
2000.016 cm ³	SAP-UNITY
19272 cm ³	SAP-UNITY
Product Length/Depth	Product Height
150 mm	71 mm
Product Width	Product Weight
54 mm	659 g
Compliances	Certifications
CE Marked	IEC 60269-1
RoHS Compliant	IEC 60269-2
	DIN 43620

Type

fuse

Special features

Live gripping lug

Application

industrial

Utilities, Solar, Wind

Amperage Rating

315 A

Fitted with:

Metal gripping lugs

Fuse size

NH2

Current type

AC

Breaking capacity

120 kA

Frequency rating - max

62 Hz

Frequency rating - min

45 Hz

Rated switching capacity

120 kA

Rated voltage AC

500 V

Class

Class gG/gL

Fuse type

Square body with knife blade contact

Accessory/spare part type

SDL-2 Solid link

FEH- Fuse extraction handle

SD12-SK Shroud kit

SD12-PB 2-phase barriers and 2 ganging links

TD2-IP20 Triple pole protection kit

Biuletyny usług serwisowych

Datasheet - 315NHG2B (PL)

Utilization category

gL/gG (cable protection/equipment protection)

Interrupt rating

120 kAIC

Fuse indicator

Combination fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Connection

Blade end

Construction

NH2

Construction size

NH2

Fuse shape

Knife blade contacts

Square body

Voltage type

AC

Suitable for

SD2-D Single pole NH Fuse base

TD2-D Tripe pole NH Fuse base

Microswitch 170H0235

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Material

Ceramic body

Quantity

3

Voltage rating

500 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia