

Eaton 32NHG000B

Catalog Number: 32NHG000B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 32A, 120 kAIC, Combination fuse status indicator, fuse, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	32NHG000B
Packing Unit	
Case Pack	
Pack	
EAN	Quantity
5027590363761	60
5027590199803	3
Gross Weight	Length
8.205 kg	420 mm
0.392 kg	83 mm
Width	Height
180 mm	140 mm
78 mm	56 mm
Volume	ERP Name
10584 cm ³	SAP-UNITY
362.544 cm ³	SAP-UNITY
Product Length/Depth	Product Height
79 mm	51 mm
Product Width	Product Weight
21 mm	119.333 g

Compliances

CE Marked

Certifications

IEC 60269-1

Electrical data

Amperage Rating

32 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

DIN 43620

Fuse size

NH000

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

Microswitch 170H0236

EBF Vertical fuse rail

EBV Vertical fuse switch-disconnectors

EBH Size 000 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia