

Eaton 400NHG2B

Catalog Number: 400NHG2B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 400A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	400NHG2B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590364751	24
5027590201513	3
Gross Weight	Length
16.474 kg	365 mm
1.978 kg	153 mm
Width	Height
320 mm	165 mm
172 mm	76 mm
Volume	ERP Name
19272 cm ³	SAP-UNITY
2000.016 cm ³	SAP-UNITY
Product Length/Depth	Product Height
150 mm	71 mm
Product Width	Product Weight
54 mm	659 g

	Compliances	Certifications
	RoHS Compliant	IEC 60269-1
defaultTaxonomyAttributeLabel	Do pobrania	
		DIN 43620

Type

fuse

Special features

Live gripping lug

Application

- industrial
- Utilities, Solar, Wind

Amperage Rating

400 A

Fitted with:

Metal gripping lugs

Fuse size

NH2

Current type

AC

Breaking capacity

120 kA

Frequency rating - max

62 Hz

Frequency rating - min

45 Hz

Rated switching capacity

120 kA

Rated voltage AC

500 V

Class

Class gG/gL

Fuse type

Square body with knife blade contact

Accessory/spare part type

- SDL-2 Solid link
- FEH- Fuse extraction handle
- SD12-SK Shroud kit
- SD12-PB 2-phase barriers and 2 ganging links
- TD2-IP20 Triple pole protection kit

Utilization category

gL/gG (cable protection/equipment protection)

Interrupt rating

120 kAIC

Fuse indicator

Combination fuse status indicator

Insulated metal gripping lugs (IMGL)

No

Connection

Blade end

Construction

NH2

Construction size

NH2

Fuse shape

Square body

Knife blade contacts

Voltage type

AC

Suitable for

SD2-D Single pole NH Fuse base

TD2-D Tripe pole NH Fuse base

Microswitch 170H0235

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Material

Ceramic body

Quantity

3

Voltage rating

500 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia