

Eaton 40NHG000B

Catalog Number: 40NHG000B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 40A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, square-body with knife blade contact

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	40NHG000B
	Packing Unit
	Case Pack Pack
EAN	Quantity
5027590363839	60
5027590201391	3
Gross Weight	Length
8.205 kg	420 mm
0.392 kg	83 mm
Width	Height
180 mm	140 mm
78 mm	56 mm
Volume	ERP Name
10584 cm ³	SAP-UNITY
362.544 cm ³	SAP-UNITY
Product Length/Depth	Product Height
79 mm	51 mm
Product Width	Product Weight
21 mm	119.333 g
Compliances	Certifications
RoHS Compliant	IEC 60269-1
CE Marked	IEC 60269-2
	DIN 43620

Electrical data

Amperage Rating

40 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

Fuse size

NH000

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

Microswitch 170H0236

EBF Vertical fuse rail

EBV Vertical fuse switch-disconnectors

EBH Size 000 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia