

Eaton 50NHM1B

Catalog Number: 50NHM1B

Fuse-link, low voltage, 50 A, AC 500 V, NH1, aM, IEC, dual indicator

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	50NHM1B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590343657	36
5027590328579	3
Gross Weight	Length
15.5 kg	475 mm
3.15 kg	137 mm
Width	Height
290 mm	155 mm
134 mm	68 mm
Volume	ERP Name
21351.25 cm ³	SAP-UNITY
1248.344 cm ³	SAP-UNITY
Product Length/Depth	Product Height
40 mm	63 mm
Product Width	Product Weight
135 mm	1050 g
Compliances	Certifications
CE Marked	IEC 60269-1
RoHS Compliant	IEC 60269-2
	DIN 43620

Electrical data

Amperage Rating

50 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Product specification

Fuse size

NH1

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

SD1-D Single pole NH Fuse base

TD1-D Tripe pole NH Fuse base

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia