

Eaton 63NHG00B

Catalog Number: 63NHG00B

Fuse-link, low voltage, 63 A, AC 500 V, NH00, gL/gG, IEC, dual indicator

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	63NHG00B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590363952	72
5027590321747	3
Gross Weight	Length
14.64 kg	350 mm
0.59 kg	102 mm
Width	Height
220 mm	215 mm
80 mm	63 mm
Volume	ERP Name
16555 cm ³	SAP-UNITY
514.08 cm ³	SAP-UNITY
Product Length/Depth	Product Height
79 mm	58 mm
Product Width	Product Weight
30 mm	197 g
Compliances	Certifications
CE Marked	IEC 60269-1
RoHS Compliant	IEC 60269-2
	DIN 43620

Electrical data

Amperage Rating

63 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Product specification

Fuse size

NH00

Insulated metal gripping lugs (IMGL)

No

Accessories

Suitable for

SD00-D Single pole NH Fuse base

TD00-D Tripe pole NH Fuse base

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Do pobrania

Biuletyny usług serwisowych

Datasheet - 63NHG00B (PL)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia