

Part number

APV 20



Painted distribution box, AP series, external dimensions 264x314x122 mm / internal dimensions 243x292x104 mm

Product description		Material properties	
Product type	Painted distribution box	Main material	Aluminium die-cast
Series	AP	Other materials	Gasket: Polyurethane (PUR) Screws: galvanized steel
Size	External dimensions 264x314x122 mm / internal dimensions 243x292x104 mm	Colour	RAL 7040 grey
Technical data		RoHs conformity	Compliant with exemption 6(c): copper alloy containing up to 4% lead by weight
IP degree of protection	IP66 / IP67	China RoHs - EFUP	50
Further technical details		REACH SVHC substances	Yes Lead
Weight	2.565,00 g	SCIP number	A4d990c2-7936-4d11-a722-eb8d5d39ca82
Operating temperature range (min, max)	-40°C...+110°C	General ordering information	
		EAN13 code	8015747001854
Packaging Information			
Packaging length	390,00 mm	Packaging height	330,00 mm
Packaging width	550,00 mm	Packaging weight	16,25 kg
Packaging volume	70,79 dm ³	Packaging description	Carton box
Packaging quantity	6 Pcs	Packaging EAN code	8015747113120
Sub-packaging weight	2,71 kg	Sub-packaging description	Plastic packaging
Sub-packaging quantity	1 Pcs	Sub-packaging EAN barcode	8015747283205