




Rating	3A 125V AC 1.5A 250V AC		Circuit Diagram	
Contact Resistance	50m ohm Max		OFF	
Insulation Resistance	DC 500V 100M ohm Min.		(ON)	
Dielectric Strength	AC 1500V 1 minute.			
Operation Temperature	-20°C~85°C			
Switch Function	4P SPST OFF-(ON) (LED independent)			

LED Rating

Red:@20mA,If=2.0VDC

Yellow:@20mA,If=2.1VDC






Green@20mA,If=2.2VDC

Material:

Frame:Black, Nylon#66

Actuator: PC,

Terminals:Copper Alloy



1830443	Yellow	Yellow
1830437	Green	Green
1830436	Red	Red
SCI BOM NO.	Actuator Color	LED Color

Tolerances ±0.3 Unless Otherwise Specified

12/19/14	何 珅	方便生產，簡化制程，統一標籤位置			△
08/22/12	柳新強	增加SCI LOGO			△
09/14/07	李日紅	R13-523-9黑底座尺寸變更增加凸包			△
Date	Name	Description			No.
Drawn	Checked	Approved	SCI BOM No	See the table	Model Name PUSH SWITCH
何 珅	李日紅	Simon	Customer No		Model No. R13-523AL-05
12/19/14	12/24-14	12/25-14	Unit	mm	Rev. 3
Shin Chin Industrial Co., Ltd.					