







Rating	3A 125V AC 1.5A 250V AC		Mounting Hole	Circuit Diagram	
Contact Resistance	50m ohm Max.			OFF	
Insulation Resistance	DC 500V 100M ohm Min.			ON	
Dielectric Strength	AC 1500V 1 minute				
Operation Temperature	-20°C~85°C				
Switch Function	4P SPST OFF-ON(LED independent)				

Material:
Frame:Black, Nylon#66
Actuator: PC
Terminals:Copper Alloy



1830438	Green	Green
1830445	Red	Red
1830444	Yellow	Yellow
SCI BOM NO.	Actuator Color	LED Color

Tolerances ± 0.3 Unless Otherwise Specified

12/19/'14	何 珅	方便生產，簡化制程，統一標籤位置					③
09/12/'12	柳新強	增加SCI LOGO					②
09/14/'07	李日紅	R13-523-9黑底座尺寸變更增加凸包					①
Date	Name	Description					No.
Drawn	Checked	Approved	SCI BOM No.	See The Table	Model Name	PUSH SWITCH	
何 珅			Customer No.		Model No.	R13-523BL-05	Rev.
12/19/'14	12/24-'14	12/25-'14	Unit	mm	Shin Chin Industrial Co., Ltd.		3