

**FOAM SWAB****41-096-0202n****Product Specification****Material:**

Head: Open-cell PU foam
Handle: ESD safe Polypropylene

Head Dimensions:

Width: 3.6mm
Thickness: 3.5mm
Length: 12.0mm

Handle Dimensions:

Width: 3.0mm
Length: 59.0 mm

Total Swab Length: 71.0 mm

Packaging: 500pcs/pkt

Contamination Features

Cleanroom compatible: ISO 4

Non-volatile Residue:

DI Water: < 0.02 mg/swab
IPA: < 0.06 mg/swab

Ion Content:

Chloride: < 0.09 ug/swab
Sulfate: < 0.08 ug/swab
Total anions: < 0.17 ug/swab

ESD safe Features

Handle Resistivity: 10×10^{10} Ohms/Sq