



FOAM SWAB

41-096-0206n



Product Specification

Material:

Head: Open-cell PU foam
Handle: ESD safe Polypropylene

Head Dimensions:

Width: 6.8mm
Thickness: 5.0mm
Length: 18.0mm

Handle Dimensions:

Width: 3.0mm
Length: 145.0mm

Total Swab Length: 163.0mm

Packaging: 100pcs/pkt

Contamination Features

Cleanroom compatible: ISO 4

Non-volatile Residue:

DI Water: < 0.01 mg/swab
IPA: < 0.05 mg/swab

Ion Content:

Chloride: < 0.08 ug/swab
Sulfate: < 0.06 ug/swab
Total anions: < 0.14 ug/swab

ESD safe Features

Handle Resistivity: 10×10^{10} Ohms/Sq