

USB 2.0 AM to AM cable, 6ft, AWG24 power supply wires

CCP-USB2P-AMAM-6



Features

- USB 2.0 AM to AM cable
- Data transfer rate up to 480 MBps
- Suitable for USB hub or HDD enclosure with type A-female connector

Specifications

Interface: USB 2.0, backward compatible with USB 1.x
Connectors: 2x USB type-A (male)
Color: black
Length: 6 ft (1.8 m)
Power supply wires: AWG24

Packaging

Q'ty in crtn, pcs	200
Crtn volume, CUM	0.037
Crtn weight, kgs	13.94
Individual package size LxWxH:	120x20x175 mm
Carton size LxWxH:	400x320x290 mm
Country of origin	CN
Barcode	8716309127486
Customs code	8544429090

System requirements

Device with the USB-A female connector

Certificates

