

Eaton EMN25 D30 GSK M15

Catalog Number: EMN25 D30 GSK M15

Eaton Crouse-Hinds series EMN NEMA manual pushbutton starter, With starter, 3 HP/5 HP, Square D starter, Copper-free aluminum, NEMA size 0, Three-pole, Polyphase, 200-230 Vac/380-575 Vac, Gasket, M15 model



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EMN NEMA manual pushbutton starter	EMN25 D30 GSK M15
	Product Length/Depth
	7.94 in
Product Height	Product Width
10.44 in	7.6 in
Product Weight	
14.17 lb	

Zdjęcie jest reprezentatywne

Horsepower

3 hp/5 hp

Manufacturer

Square D

Material

Copper-free aluminum

Number Of Poles

Three-pole

NEMA size

0

Phase

Poly-phase

Special features

Gasket

Type

M15 model

Voltage rating

200-230 Vac/380-575 Vac

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

Enclosure

With starter



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia