




FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人

PART NUMBER: RJ45C-02-△

"△"	CRUST MATERIAL
NO LETTER	ABS(SILVER)
BK	PA(BLACK)
OTHER COLOR CAN BE CUSTOMIZED	

SPECIFICATIONS:
1.OPERATION TEMPERATURE: -25℃~ +55℃ (NO FREEZING) .
2.OPERATION HUMIDITY: 45~ 85%RH (NO CONDENSATION) .
3.HEAD PORT: RJ45 FEMALE.
4.BACK PORT: RJ45 FEMALE.
5.TORQUE: 0.6Nm Max. APPLIED TO NUT.
6.GENERAL TOLERANCE:0-18mm=±0.25, 18-80mm=±0.52.

MATERIAL:
1.BODY: ABS(SILVER)/PA(BLACK)

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称	PANEL MOUNTING TYPE USB2.0 CONNECTOR			UNIT 单位	mm
DWG NO. 图号	RJ45C-02			SCALE 比例	1.2 : 1
FILE NAME 档案名称	RJ45C.DWG	DRAWN 制图	HCP 2023/12/11	SHEET 张	1/1
				REV. 更改	1