




FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人

PART NUMBER: USB-10-△

"△"	CRUST COLOR
NO LETTER	SILVER
BK	BLACK
OTHER COLOR CAN BE CUSTOMIZED	

SPECIFICATIONS:

1. OPERATION TEMPERATURE: -25°C ~ +55°C (NO FREEZING) .
2. OPERATION HUMIDITY: 45 ~ 85%RH (NO CONDENSATION) .
3. TRANSMISSION RATE: ≥100MB/s.
4. HEAD PORT: USB3.0 B TYPE FEMALE.
5. BACK PORT: USB3.0 A TYPE FEMALE.

MATERIAL:

1. BODY: AL ALLOY.

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称	PANEL MOUNTING TYPE USB3.0 CONNECTOR			UNIT 单位	mm
DWG NO. 图号	USB-10			SCALE 比例	1.2 : 1
FILE NAME 档案名称	塑料转接器 USB3.0.DWG	DRAWN 制图	YDY 2022/07/01	SHEET 张	1/1
				REV. 更改	1