

1

2

3

4

5

6

7

FOR
客户名称APPROVED
客户确认签字ATTN
销售负责人

A

B

C

D

E




A

B


C

D

E



PANEL CUTOUT



SEAL RING

PART NUMBER: USB-19-△

"△"	CRUST COLOR
NO LETTER	SILVER
BK	BLACK
OTHER COLOR CAN BE CUSTOMIZED	

SPECIFICATIONS:

1. OPERATION TEMPERATURE: -25°C ~ +55°C (NO FREEZING) .
2. OPERATION HUMIDITY: 45 ~ 85%RH (NO CONDENSATION) .
3. TRANSMISSION RATE: ≥30MB/s.
4. HEAD PORT: USB2.0 A TYPE FEMALE.
5. BACK PORT: USB2.0 A TYPE MALE.

MATERIAL:

1. BODY: AL ALLOY.

BRAND 品牌

ONPOW 欧宝龙®**红波按钮制造有限公司**

ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.

TITLE 名称		PANEL MOUNTING TYPE USB2.0 CONNECTOR				UNIT 单位	mm				
DWG NO. 图号		USB-06		SCALE 比例		1.2 : 1	SIZE 图纸	A4			
FILE NAME 档案名称		金属转接线 USB2.0.DWG		DRAWN 制图		YDY 2022/07/01		SHEET 张	1/1	REV. 更改	1

1

2

3

4

5

6

7