

1

2





3

4

5

6

7

FOR  
客户名称APPROVED  
客户确认签字ATTN  
销售负责人

SEAL RING

PANEL CUTOUT

PART NUMBER: USB-19C-△

| "△"                           | CRUST COLOR |
|-------------------------------|-------------|
| NO LETTER                     | SILVER      |
| BK                            | BLACK       |
| OTHER COLOR CAN BE CUSTOMIZED |             |

**SPECIFICATIONS:**

1. OPERATION TEMPERATURE: -25°C ~ +55°C (NO FREEZING) .
2. OPERATION HUMIDITY: 45 ~ 85%RH (NO CONDENSATION) .
3. TRANSMISSION RATE: ≥30MB/s.
4. HEAD PORT: USB2.0 A TYPE FEMALE.
5. BACK PORT: USB2.0 A TYPE MALE.

**MATERIAL:**

1. BODY: ABS(SILVER)/PA(BLACK)

BRAND 品牌

**ONPOW 欧宝龙®****红波按钮制造有限公司**

ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.

|                   |  |                                      |  |                                                                                       |  |                |            |            |     |            |   |
|-------------------|--|--------------------------------------|--|---------------------------------------------------------------------------------------|--|----------------|------------|------------|-----|------------|---|
| TITLE<br>名称       |  | PANEL MOUNTING TYPE USB2.0 CONNECTOR |  |  |  | UNIT<br>单位     | mm         |            |     |            |   |
| DWG NO.<br>图号     |  | USB-19C                              |  | SCALE<br>比例                                                                           |  | 1.2 : 1        | SIZE<br>图纸 | A4         |     |            |   |
| FILE NAME<br>档案名称 |  | 塑料转接线<br>USB2.0.DWG                  |  | DRAWN<br>制图                                                                           |  | YDY 2022/01/24 |            | SHEET<br>张 | 1/1 | REV.<br>更改 | 1 |