

Socket outlet combination

## STV 912-K



### STV 912-K

Socket outlet combination

CUSTOMIZABLE

Productnumber: 72941201

Dimensions: 200 x 400 x 122 mm

Socket outlet combination, protection class IP44, ready for connection, according to EN 61439-3, high mechanical strength, temperature-resistant, can be combined

Cable insertions:

Top: Pre-embossing 8 x M20, 1 x M25/32

Bottom: Pre-embossing 8 x M20, 1 x M32/25

Left: Pre-embossing 4 x M20/25

Right: Pre-embossing 4 x M20/25

Rear: Pre-embossing 4 x M20/25

equipped with:

- 1 x Miniature circuit breaker B16A, 1-pin
- 1 x Miniature circuit breaker C 16 A, 3p
- 1 x Residual Current Circuit Breaker (RCCB), 40/0.03A, 4-pole, type A
- 2 x SCHUKO® plug socket (on front), 230V
- 1 x CEE plug socket outlet (on front) 16A, 400V

Accessories supplied:

Attachment bushes: 2x M25, 2x M32, sealing plugs, masking and labelling strips



## Technical Data

### Built-in devices

|                                                                    |   |
|--------------------------------------------------------------------|---|
| Residual Current Circuit Breaker (RCCB), 40/0.03A, 4-pole, type A: | 1 |
| Miniature circuit breaker B16A, 1-pin:                             | 1 |
| Miniature circuit breaker C 16 A, 3p:                              | 1 |
| SCHUKO® plug socket (on front), 230V:                              | 2 |
| CEE plug socket outlet (on front) 16A, 400V:                       | 1 |

### electrical characteristics

|                              |       |
|------------------------------|-------|
| Rated insulation voltage AC: | 400 V |
| Protection class:            | II    |
| Type of protection:          | IP44  |
| Number of N-potentials:      | 1     |
| Number of rows:              | 1     |
| Number of modules per row:   | 9     |
| with N terminal:             | yes   |
| with PE terminal:            | yes   |

### Colours

|                   |      |
|-------------------|------|
| Base unit colour: | grey |
| Cover colour:     | grey |

### Dimensions

|         |        |
|---------|--------|
| Width:  | 200 mm |
| Length: | 400 mm |
| Height: | 122 mm |

### Material characteristics

|                                         |     |
|-----------------------------------------|-----|
| UV-resistant:                           | yes |
| Halogen free:                           | yes |
| Flammability class according with UL94: | V2  |

### Material characteristics

|                                                    |        |
|----------------------------------------------------|--------|
| Glow-wire flammability according to EN 60695-2-11: | 850 °C |
| Industry quality:                                  | yes    |

### mechanical properties

|                    |               |
|--------------------|---------------|
| Type of fastening: | Wall mounting |
| Impact strength:   | IK08          |

### Ambient conditions

|                              |                         |
|------------------------------|-------------------------|
| max. relative humidity 25°C: | 95 %                    |
| max. relative humidity 40°C: | 50 %                    |
| Min. ambient temperature:    | -25 °C                  |
| Max. ambient temperature:    | 40 °C                   |
| 24h ambient temperature:     | 35 °C                   |
| Installation location:       | protected outdoor areas |

### Material

|                         |                                       |
|-------------------------|---------------------------------------|
| Base unit material:     | Polycarbonate, glass-fibre reinforced |
| Cover material:         | Polycarbonate, glass-fibre reinforced |
| Sealing material:       | Polyurethane                          |
| Cover screw material:   | Polyamide, glass-fibre reinforced     |
| Hinged window material: | Polycarbonate                         |

## Cable gland

